



# ANT-SS900

## 868-915MHz Compressed Whip Antenna

Electrical Specifications	
Frequency Range	868-915MHz
Nominal Impedance	50 $\Omega$
Maximum Input Power	50W
Radiation Pattern	Omni-directional
Polarization	Vertical
VSWR	$\leq 1.5$
Connector	SMA male straight

Mechanical Specifications	
Material	Rugged Antenna
Antenna dimensions	51mm x 8mm
Antenna weight	6g
Ambient Temperature	-40°C to 60°C

<b>Order Code</b>	ANT-SS900
-------------------	-----------

Accessories	
Description	Order Code
PCB mount SMA connector	SMACONNECTOR
Right angled PCB mount SMA connector	SMARACONNECTOR
SMA bulkhead Jack	SMAENDBLKHD-JK
U.FL to SMA female jack 100mm	ARW-CAB-SMA-UFL-10

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LPRS:](#)

[ANT-SS900](#)